

Elcometer 1800 Density Cup

The Elcometer 1800 is a stainless steel precision cup for determining the specific gravity or density of paints and similar products.

The density cup consists of a cylindrical container and lid with a hole for the exhaust of excess liquid.

**STANDARDS:**

ASTM D 891-B, ASTM D1475, DIN 53217-2,
FTMS 141 4183, ISO 2811-1, JIS K 5600-2-4,
NBN T22-110, NFT 30-020

Technical Specification

C

Part Number	Description	Volume/ Capacity	Certificate
K0001800M001	Elcometer 1800/1 Density Cup stainless steel	50cc	
K0001800M002	Elcometer 1800/2 Density Cup stainless steel with calibration certificate	50cc	•
K0001800M005	Elcometer 1800/5 Density Cup stainless steel	100cc	
K0001800M006	Elcometer 1800/6 Density Cup stainless steel with calibration certificate	100cc	•

How to use a Density Cup:

- Weigh the Cup and Lid when empty
- Fill with the liquid
- Place lid on the Cup, removing excess liquid*
- Weigh the Density Cup when full
- Divide the weight by the cup volume/capacity to determine the Specific Gravity

*Each Cup has an escape hole in the lid to allow excess liquid to escape. Any excess liquid should be removed before weighing.

The formulae for calculating Density and Specific Gravity are:

Density =

Weight
Unit Volume

Note: 50cc = 50cm³ = Volume
100cc = 100cm³ = Volume

Specific Gravity =

Density of the Material
Density of Water at the Same Temperature

Алматы (7273)495-231
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +7(7172)727-132

Киргизия +996(312)96-26-47

Elcometer 8720 Compact Balance

The Elcometer 8720 Compact Balance is very easy to use and offers extensive weighing functions selectable by the user.

- Weighing range from 0 - 1,210g (0 - 42.7oz)
- Backlit LCD display
- 130 x 130mm stainless steel weighing plate



Technical Specification

C

Part Number	Description		Certificate
UK 240V	EUR 220V	US 110V	
K0UK8720M001	K0008720M001	K0US8720M001	Elcometer 8720 Compact Balance
K0UK8720M001C	K0008720M001C	K0US8720M001C	Elcometer 8720 Compact Balance - Certified •
Range	0 - 1,210g (0 - 42.7oz)		
Reproducibility	0.01g (0.0004oz)		
Linearity	±0.03g (0.001oz)		
Dimensions	167 x 250 x 85mm (6.6 x 9.8 x 3.3")		
Weight	2kg (4.4lb)		
Packing List	Elcometer 8720 Compact Balance, power cable and operating instructions		

Алматы (7273)495-231
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Владимир (4922)49-43-18
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Ноябрьск (3496)41-32-12
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +7(7172)727-132

Киргизия +996(312)96-26-47

<https://elcometer.nt-rt.ru/> || erj@nt-rt.ru